



Traverse®

36" x 34" Vikrell® shower with Aging in Place backerboards, center drain

72500106



Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Modern subway tile design
- Full-length shelf provides generous storage
- Easy-to-clean, durable high-gloss finish
- Factory-installed Aging in Place backerboards for future grab bar installation

Material

- Compression-molded from our exclusive solid Vikrell® material

Installation

- Pro4™ installation system features a two-piece back wall design, enabling one-person handling and installation
- Alcove
- Center drain
- Caulk-free installation

Recommended Products/Accessories

- 80001012 12" straight grab bar
- 80001018 18" straight grab bar
- 80001024 24" straight grab bar
- 5690-33 Headerless frameless pivot shower door
- 5699-33 Headerless frameless pivot shower door

Included Components

- 72301100 36" x 34" Vikrell® shower base, center drain
- 72502100 36" x 72-1/4" Vikrell® shower back wall
- 72505106 34" x 72-1/4" Vikrell® shower end wall set with Aging in Place backerboards



Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description



	0	White
---	---	-------

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

6-21-2026 20:33 - US/CA



Note: Right and left end walls are the same, only mirrored.

Technical Information

All product dimensions are nominal.

Drain location:	Center
Weight:	105 lbs (47.6 kg)
Minimum flat for door:	2-1/2" (64 mm)
Maximum door height:	72" (1829 mm)
Maximum door width:	32-9/16" (827 mm)

Notes

Install this product according to the installation instructions.