



# Traverse® 48" x 72-1/4" Vikrell® shower back wall 72522100



### Features



- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Modern subway tile design
- Full-length shelf provides generous storage
- Easy-to-clean, durable high-gloss finish

### Material

- Compression-molded from our exclusive solid Vikrell® material

### Installation

- Pro4™ installation system features a two-piece back wall design, enabling one-person handling and installation
- Alcove
- Caulk-free installation
- Must be installed with GUARD+ 7232 series shower base and Traverse subway tile 7250 series end wall set



### Recommended Products/Accessories

- 581075-48 Frameless sliding shower door
- 547808-48 Frameless sliding shower door
- 5475-48 Frameless sliding shower door
- 5970-48 Framed sliding shower door
- 5976-48 Framed sliding shower door
- 5960-46 Framed sliding shower door
- 5960-48 Framed sliding shower door



### Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662

### STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

#### Color Code Description

|  |   |       |
|--|---|-------|
|  | 0 | White |
|--|---|-------|

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

4-16-2026 20:24 - US/CA



**Traverse®**  
48" x 72-1/4" Vikrell® shower back wall  
**72522100**

No image available.  
This product is a component and not intended to be a standalone installation.

**Technical Information**

All product dimensions are nominal.

|                      |                    |
|----------------------|--------------------|
| Drain location:      | Center             |
| Weight:              | 39.3 lbs (17.8 kg) |
| Maximum door height: | 72" (1829 mm)      |
| Maximum door width:  | 44-9/16" (1132 mm) |

**Notes**

Install this product according to the installation instructions.