

### Features

- Solid metal construction
- G 1/2" thread connection
- Durable KOHLER finishes resist corrosion and tarnishing
- Leak-free ceramic disc valve with lifetime warranty
- Includes handshower (K-74035T-4)
- Lever handle
- Compliments most Kohler product lines

### Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552 (K-74035T-4)
- GB 18145-2014

### Installation Notes

Install this product according to the installation guide.

## EXPOSED WALL-MOUNT SHOWER MIXER

# K-73195T-4


## ALSO K-74035T-4




### Specified Model

Model	Description	Color/Finished
K-73195T-4	Taut exposed wall-mount shower mixer	CP: Polish chrome
K-74035T-4	Taut exposed wall-mount shower mixer	CP: Polish chrome

For a full range of color finishes in your market please contact your local Kohler representative.



**Flow Curve For K-73195T-4**




**Flow Curve For K-74035T-4**

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

### Product Diagram

### ก๊อกผสมเย็นอาบแบบติดผนัง **K-73195T-4** และ K-74035T-4



#### คุณลักษณะ

- ผลิตจากโลหะ
- เกลียวข้อต่อ G1/2 นิ้ว
- วัสดุเคลือบผิวพิเศษของโคห์เลอร์ คงทน เงางาม
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- พร้อมหัวฝักบัวสายอ่อน (K-74035T-4)
- มือบิดแบบก้านโยก
- เหมาะกับผลิตภัณฑ์ส่วนใหญ่ของโคห์เลอร์

#### มาตรฐาน

คุณสมบัติตามมาตรฐาน :

- มอก. 2066-2552 (K-74035T-4)
- GB 18145-2014


#### ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


#### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-73195T-4	ก๊อกผสมเย็นอาบแบบติดผนัง รุ่นทอธ	CP: สีโครมเงา
K-74035T-4	ก๊อกผสมเย็นอาบแบบติดผนังพร้อมฝักบัวสายอ่อน รุ่นทอธ	CP: สีโครมเงา

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน



กราฟแสดงอัตราการไหล K-73195T-4




กราฟแสดงอัตราการไหล K-74035T-4

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

#### ภาพแสดงผลิตภัณฑ์