

Features

- Vitreous China
- Without Overflow
- Above counter
- Symmetrical Design



Recommended Accessories

- Bottle Trap (75823IN)

COMPATIBLE FAUCETS	
Description	SKU Code
ALEO LAV FAUCET WITH DRAIN	K-72275IN-4
ALEO+ SC LAV FAUCET WITH DRAIN	72312IN-4-CP
TAUT SC LAV FAUCET WITH DRAIN	74013IN-4-CP
HINT SC LAV FAUCET WITH DRAIN	97060IN-4-CP
FAIRFAX SINGLE CONTROL LAVATORY WITH LEVER HANDLE AND DRAIN	K-8657IN-CP
CABRIOLE SINGLE CONTROL LAVATORY FAUCET WITH LEVER HANDLE WITHOUT DRAIN	K-8600IN-1ND-CP
CANDIDE SINGLE CONTROL LAVATORY FAUCET WITH LEVER HANDLE WITHOUT DRAIN	K-660IN-ND-CP
VITEO SINGLE CONTROL LAVATORY FAUCET WITH LEVER HANDLE WITHOUT DRAIN	K-5695IN-4ND-CP
EOLIA SINGLE CONTROL LAVATORY FAUCET WITH LEVER HANDLE WITHOUT DRAIN	K-8620IN-ND-CP
WAVE SINGLE CONTROL LAVATORY FAUCET WITH LEVER HANDLE & POP-UP DRAIN	K-9076IN-CP
PURIST SINGLE CONTROL LAVATORY FAUCET WITH DRAIN	K-14402IN-4A-CP
KUMIN SC LAV FAUCET WITH DRAIN	98827IN-4-CP
COMPOSED SC SIDE MOUNT LAV FAUCET W/D	73050IN-7-CP
MARGAUX LAVATORY SINGLE CONTROL FAUCET	16230IN-4-CP
NATEO MONOBLOCKSGL CONTROL LAV FAUCET	K-18000IN-ND-CP
SIROCCO DUAL HANDLE LAVATORY FAUCET	8611IN-7ND-CP
TOOBI SINGLE CONTROL LAV FAUCET	7329IN-9ND-CP
STANCE SC LAVATORY FAUCET	14760IN-4ND-CP
QUALIS SC LAV WITHOUT DRAIN	13523IN-4ND-CP


KOHLER® Ten-Year Limited Warranty

See website for detailed warranty information.

Available Color/ Finishes

Color tiles intended for reference only

Color	Code	Description
	0	White




Notes

Install this product according to the installation instructions.

Product does not have an overflow.

*Spout must be 3.9" (99mm) long (min) for adequate clearance into the bathroom sink.

NOTICE: Counter cutting should be done using the cut-out template provided with the product. Kohler is not responsible for cutout errors.



Technical Information

All Product Dimensions are nominal

Lavatory configuration	Single
Installation	Above counter
Bowl area	Length: 16 1/4" (413 mm) Width: 18 1/8" (460mm) Height: 4 15/16" (125mm) Depth: 3 1/4" (82mm)
Drain hole	Ø41.65 - 46.5 mm
Template	1293914-IN01