

Features

- Vitreous China
- Without Overflow
- Above counter
- Large wash area



Recommended Accessories

- Bottle Trap (75823IN-CP)
- Grid Drain without Overflow (20746IN-CP)
- Ceramic Drain without Overflow (20740IN-0)

| Material | Description |
|----------------|--|
| 99858IN-4-CP | BEITOU SINGLE CONTROL TALL LAV FAUCET |
| 97347IN-4-CP | AVID SC TALL LAV FAUCET WITH DRAIN |
| 73053IN-4-CP | COMPOSED SC JOYSTICK TALL LAV FCT. W/D |
| 73159IN-7-CP | COMPOSED SC SIDE MOUNT TALL LAV FCT. W/D |
| 10861IN-4ND-CP | SINGULIER SINGLE LEVER TALL LAV FAUCET |
| 72337IN-4ND-CP | ALEO+ TALL LAV FAUCET W/O DRAIN |
| 72298IN-4-CP | ALEO TALL LAV FAUCET W/ DRAIN |
| 37334IN-4-CP | STRAYT TALL PILLAR TAP |
| 11546IN-4-CP | SINGULIER TALL PILLAR LAVATORY FAUCET |
| 20071IN-4-CP | ALEO+ PILLAR TAP, TALL |
| 20070IN-4-CP | ALEO PILLAR TAP, TALL |


KOHLER® Ten-Year Limited Warranty

See website for detailed warranty information.

Available Color/ Finishes

Color tiles intended for reference only

| Color | Code | Description |
|---|------|-------------|
|  | 0 | White |



Notes

Install this product according to the installation instructions.

Product does not have an overflow.

*Spout must be 3.9" (99mm) long (min) for adequate clearance into the bathroom sink.

NOTICE: Counter cutting should be done using the cut-out template provided with the product. Kohler is not responsible for any cutout errors.

Technical Information

All Product Dimensions are nominal

| | |
|------------------------|---|
| Lavatory configuration | Single |
| Installation | Above Counter |
| Bowl area | Length: 35 1/32" (890 mm) Width: 15 5/8" (397 mm) Height: 5 1/2" (139 mm) Depth: 4 1/2" (114 mm) |
| Drain hole | Ø41.65 - Ø46.5 mm |
| Template | 1293912-IN7 |