

### Features

- 6-11/16" (170 mm) spout reach.
- Tall height is ideal for vessel-style sinks.
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar).
- Laminar flow controls deliver a graceful stream while conserving water.
- Includes metal touch-activated drain with 1-1/4" tailpiece.
- Coordinate with your choice of Components bathroom sink faucet handles for a personalized design.

### Material

- Premium metal construction for durability and reliability.
- KOHLER finishes resist corrosion and tarnishing.

### Installation

- Widespread or remote valve.

### Water Conservation & Rebates

- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System.

### Required Products/Accessories

- K-77974-4 bathroom sink handles with Lever design
- or
- K-77974-8 bathroom sink handles with Oyl design
- or
- K-77974-9 bathroom sink handles with Industrial design
- or
- K-77963-8A bathroom sink rocker handle

### Recommended Products/Accessories

- K-23726 Drain treatment
- K-23723 Faucet cleaner



### Codes/Standards

ASME A112.18.1/CSA B125.1  
NSF/ANSI 61  
NSF/ANSI 372  
All applicable US Federal and State material regulations  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
California Energy Commission (CEC)


### KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

| Color                                                                               | Code | Description                              |
|-------------------------------------------------------------------------------------|------|------------------------------------------|
|  | CP   | Polished Chrome                          |
|  | BN   | Vibrant® Brushed Nickel                  |
|  | BL   | Matte Black                              |
|  | 2MB  | Vibrant® Brushed Moderne Brass           |
|  | 3TR  | Vibrant® Ombré Titanium/Rose Gold        |
|  | 3RS  | Vibrant® Ombré Rose Gold/Polished Nickel |



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 1.2 gal/min (4.5 l/min)  
Pressure: 60 psi (4.1 bar)  
Drain included: Yes

#### Spout:

Spout reach: 6-11/16" (170 mm)

### Notes

Install this product according to the installation instructions.