

Features

- Vitreous china
- Round-front bowl
- Back-to-Wall
- Includes quiet close seat or nightlight seat
- Includes side push button for manual flush
- Simply hold your hand over the sensor to activate
- Powered by 2 D batteries (included)
- Wash down flushing system
- Dual flush 3/4.5 liter per flush
- 185 mm rough-in for P-trap
- 650 x 394 x 800 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- AS 1172
- BS:EN 997
- MS 1552
- SNI 03-0797
- TIS 792
- ASME 112.19.2/CSA B45.1
- GB 6952
- PNS 156
- SS 574


Technical Information

Fixture:	
Configuration	two-piece, round-front
Water per flush	3/4.5 liter
Passageway	51 mm
Water area	127 x 102 mm
Water depth from rim	220 mm
Seat post hole centers	140 mm

TOUCHLESS TWO-PIECE TOILET WITH SEAT

K-78316K-TF

ALSO K-78470K-TF



Included Components:	
Tank	K-77784K-TF
Bowl	K-77713K
Quiet-Close seat or Nightlight seat	K-76417K or K-77858K
Tank cover	1329165
P-trap connector assy	1138552

Installation Notes


Install this product according to the installation guide.

Specified Model

Model	Description	Color/Finished
K-78316K-TF	ModernLife touchless two-piece toilet, P-trap with nightlight seat	0: White
K-78470K-TF	ModernLife touchless two-piece toilet, P-trap with quiet-close seat	0: White

Required Accessories		Color/Finished
1065832	Water supply hose, stainless	CP: Polished Chrome
1265885-SP	Shut off valve	CP: Polished Chrome

Dimensions are approximate.
Unit: mm



Product Diagram