



**McAllister®**  
23-1/2" undermount single-bowl kitchen sink  
**97447**

**Features**

- No faucet holes; requires wall- or counter-mount faucet
- 8" (203 mm) depth
- 3-3/4" (94 mm) drain opening
- Stainless steel with luster finish

**Material**

- Premium 18-gauge stainless steel

**Installation**

- Undermount

**Recommended Products/Accessories**

- K-23726 Drain treatment
- K-23729 Stainless steel cleaner




**Codes/Standards**

ASME A112.19.3/CSA B45.4

**STERLING® Stainless Steel Sinks  
Lifetime Limited Warranty**

See website for detailed warranty information.



**Technical Information**

All product dimensions are nominal.

- Basin configuration: Single Bowl
- Bowl area:
  - Length: 21" (533 mm)
  - Width: 15-1/4" (387 mm)
  - Bowl depth: 7-3/4" (197 mm)
  - Water depth: 7-3/4" (197 mm)
- Drain hole: 3-5/8" (92 mm)
- Template: 1315840-7, required, included

**Notes**

Install this product according to the installation instructions.