



Latitude® 25" top-mount/undermount single-bowl utility sink 995



Features

- One hole predrilled and two additional locations marked on the sink to create additional holes if needed
- 12-1/4" depth

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

Recommended Products/Accessories

K-23726 Drain treatment

K-23733 Vikrell® cleaner

Optional Products/Accessories

7400 Stainless Steel Sink Drain and Strainer



Codes/Standards

CSA B45.5/IAPMO Z124

All applicable US Federal and State material regulations

IAPMO Certification


STERLING® Vikrell® or Acrylic Kitchen and Utility Sinks Lifetime Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Basin configuration:	Single Bowl
Bowl area (Only):	Length: 22" (559 mm) Width: 16" (406 mm) Bowl depth: 12-1/4" (311 mm) Water depth: 12-1/4" (311 mm)
Number of deck holes:	3
Faucet hole(s):	1-3/8" (35 mm)
Drain hole:	3-1/2" (89 mm)
Template:	1148620-7, required, included

Notes

Install this product according to the installation instructions.