

# VM36H1D18F Cartesian<sub>™</sub> - Specification Sheet

#### Features


- Modular Vanity Build arrays both stacked and ganged
- Mates to both H1D18 (7.5" high) & H2D18 (15" high) Series
- Handleless ergonomic continuous drawer
- Includes 4 glass organizing bins

#### Construction

- All aluminum and glass construction designed for disassembly and recycle, aluminum structural frame and drawer sides, glass drawer fronts, and safety backed glass drawer bottom
- Heavy duty, full extension, soft close drawers slides
- · Constructed for wall hanging loads with stone tops
- Glass fronts and optional side kits are replaceable
- Includes installation hardware using secure structural bolts
- Glass side kits sold separately

# **Codes / Standards Applicable**

- Night Light Option is ETL certified to:
  - UL 2108
  - CSA Standard C22.2 No. 12



Two H2 - 15" (381 mm) Cartesian vanities stacked Total height 30" (762 mm)

# **Dimensions**


Height: 7-1/2" (191 mm)

Width: 36-1/8" (918 mm) - with side kits installed

Depth: 18-3/4" (476 mm)

# **Configurable Options**

- Choice of front Tip out, split plumbing drawer, or full width drawer
- Integrated LED night light (L) Light bar built into top frame provides drawer illumination
- Glass finish options: Mirror, patterned glass, and back painted glass - gloss or matte
- Other widths available 12" (308 mm) / 24" (613 mm) / 30" (765 mm)
- 15" (381 mm) drawer height available H2
- Larger depth available 21-3/4" (552 mm) D21



					Model Nulliber Key		
	Width	Height	Depth	Drawer Style	Glass Finish		Night light Option
VM	36	H1	D18	F = Full	11 = Tinted Grey Mirror 20 = Black 21 = White	22 = Beach 26 = Matte White 27 = Matte Gray 28 = Matte Black 60 = Reeded White 61 = Reeded Brass	N = Base Unit (Not Included) L = 5000K S = Selectable 2700K / 4000K
						12 = Satin Bronze	

# **Electrical System**

Night light option - 12VDC plug-in transformer
 Locate wall outlet as per installation instructions 209-1231

#### **Add-On Accessories**

- Robern Engineered Stone Tops and porcelain sink available
- Assorted glass bins:
  - Divided storage (GLASSBIN6.38)
- Small (GLASSBIN3.25)
- Medium (GLASSBIN5.25)
- Large (GLASSBIN8.5)

# -34-1/2" (876 mm)

Top view for plumbing and sink clearance

# **Modular Kits**

Available in 4 heights (based on final configuration)

- Side kits (Single):
  - 7-1/2" (VM1SKH1D18##)
  - 22-1/2" (VM1SKH3D18##)
- Side kits (Pair):
  - 7-1/2" (VM2SKH1D18##)
  - 22-1/2" (VM2SKH3D18##)
- · Ganging kits:
  - 7-1/2" (VMGKITH1)
  - •22-1/2" (VMGKITH3)

• 22-1/2" (VMAKITH3)

- Alcove finishing kits:
- 7-1/2" (VMAKITH1)


• 30" (VM2SKH4D18##)

• 15" (VM1SKH2D18##)

• 30" (VM1SKH4D18##)

• 15" (VM2SKH2D18##)

- 15" (VMGKITH2)30" (VMGKITH4)
- 15" (VMAKITH2)
- 30" (VMAKITH4)



Side views for plumbing and sink clearance with door front

Front view with side kits

### **Installation Notes**

Install this product according to the installation guide 209-1231.

- The Robern Engineered Stone Tops and porcelain sinks are recommended for this vanity.
- · Special site preparation is required. Wall bracing and Robern supplied hardware are recommended.
- If a sink will be installed, the plumbing must be roughed into the plumbing cutout area of the vanity. Refer to the sink rough-in and the vanity rough-in for proper placement. The water supply and drain lines must be installed before installing the vanity.