# Mira Decor Dual

## Electric Shower

COLD MAINS

2 YEAR WARRANTY



## Thoughtfully designed to meet all your needs

### Product Information

| Description | Colour | Product No. |
|---|---|---|
| Mira Decor Dual 9.5KW | White | 41521W-WH |
| Mira Decor Dual 9.5KW | Warm Silver | 41521W-SL |
| Mira Decor Dual 9.5KW | Bronze | 41521W-BZ |
| Mira Decor Dual 9.5KW | Black Onyx | 41521W-BL |
| Mira Decor Dual 10.8KW | White | 41522W-WH |
| Mira Decor Dual 10.8KW | Warm Silver | 41522W-SL |
| Mira Decor Dual 10.8KW | Black Onyx | 41522W-BL |
| Mira Decor Dual 10.8KW | Bronze | 41522W-BZ |

### Features & Benefits

| |
|---|
| **Temperature control** |
| Pressure stabilised temperature control |
| **Easy to fit** |
| Retrofits onto inlets of most Mira electric showers |
| Left-hand water and cable entry points |
| **Easy to service** |
| Easy filter access |
| **For your customer** |
| Separate power and temperature controls |
| Push button on/off |
| Low power setting saves water and energy |
| Clearscale™ reduces limescale by up to 50% |
| Modern aesthetics with range of colours |
| Easy to use diverter allows for relaxing overhead shower or invigorating handshower with wide spray coverage |
| 250 mm easy clean overhead with rub-clean nozzles |
| 4 spray 120 mm optimised easy clean showerhead with rub-clean nozzles |
| Easy clean smooth hoses |

To download other resources, and for more information and advice on our products just visit:

**www.mirashowers.co.uk**

mira SHOWERS

# Product Specification

Tech Details


| Temperature Control |
|---|
| Control type: Pressure stabilised |
| **Installation** |
| Power options: 9.5kW & 10.8kW 240V AC (9.9kW 230V AC) |
| Supply voltage: 230v ± 10% |
| Supply rating: 40 amp (9.5kW), 45 amp (10.8kw) |
| Terminal Block connections: Maximum 10mm$^2$ |
| Water entry points: Left (rising, falling & rear) |
| Cable entry points: Left (rising, falling & rear) |
| Inlet connections: 15 mm plastic stub, compression or push-fit fittings |
| Outlet connections: ½" BSP Male |
| **Supply Conditions (Mains Cold)** |
| Minimum maintained pressure: 1.0 bar (10 metre head) |
| Maximum maintained pressure: 5.0 bar (50 metre head) |
| Maximum static pressure: 10.0 bar (100 metre head) |

| Performance |
|---|
| Temperature stability: ± 6°C |
| **Safety Features** |
| Phased shutdown: No |
| Factory set to safe max temp: No |
| Mira Sensi-flo™: No |
| **Accessories** |
| Wide range of accessories available at www.mirashowers.co.uk |
| **Approvals** |
| BEAB approved |
| Kiwa certified |

BEAB Approved Intertek

kiwa certified

## Dimensions




To download other resources, and for more information and advice on our products just visit:

www.mirashowers.co.uk

mira SHOWERS