



**McAllister®**

31-3/4" undermount double-bowl kitchen sink, 40 pack  
**F11409**

### Features

- No faucet holes; requires wall- or counter-mount faucet
- 8-5/16" (203 mm) depth
- 3-3/4" (94 mm) drain opening
- Stainless steel with luster finish
- Large/small bowls
- Project pack: Supplied 40 sinks per order
- Sink drain with strainer sold separately

### Material

- Premium 18-gauge stainless steel

### Installation

- Undermount
- Can be installed with or without reveal

### Recommended Products/Accessories

7400 Stainless Steel Sink Drain and Strainer  
11862 Sink Rack  
11863 Sink Rack  
K-23729 Stainless steel cleaner




### Codes/Standards




ASME A112.19.3/CSA B45.4

### **STERLING® Stainless Steel Sinks Lifetime Limited Warranty**

See website for detailed warranty information.



Mounting bracket assembly provides a secure installation.



## Technical Information

All product dimensions are nominal.

Basin configuration: Large Bowl on Left

Min. base cabinet width: 36" (914 mm)

Bowl area (Basin #1): Length: 14-1/4" (362 mm)  
Width: 18-1/2" (470 mm)  
Bowl depth: 8" (203 mm)  
Water depth: 8" (203 mm)

Bowl area (Basin #2): Length: 14-1/4" (362 mm)  
Width: 15-3/4" (400 mm)  
Bowl depth: 8" (203 mm)  
Water depth: 8" (203 mm)

Drain hole: 3-3/4" (95 mm)

Template: Undermount, 1315847-7, required, included

## Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.

Use the supplied cut-out template to select either a hidden or exposed rim.