



McAllister®
32" undermount double-bowl kitchen sink, 40 pack
F11444

Features

- No faucet holes; requires wall- or counter-mount faucet
- 8-9/16" (217 mm) depth
- 3-5/8" (92 mm) drain opening
- Stainless steel with luster finish

Material

- Premium 18-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

7400 Stainless Steel Sink Drain and Strainer

11861 Sink Rack

K-23729 Stainless steel cleaner




Codes/Standards

ASME A112.19.3/CSA B45.4


STERLING® Stainless Steel Sinks

Lifetime Limited Warranty


See website for detailed warranty information.





Mounting bracket assembly provides a secure installation.



Reveal



No Reveal



Technical Information

All product dimensions are nominal.

Basin configuration: Equal Bowls

Min. base cabinet width: 36" (914 mm)

Bowl area (Left): Length: 14-1/16" (357 mm)
Width: 15-3/4" (400 mm)
Bowl depth: 8-9/16" (218 mm)
Water depth: 8-1/16" (205 mm)

Bowl area (Right): Length: 14-1/16" (357 mm)
Width: 15-3/4" (400 mm)
Bowl depth: 8-9/16" (218 mm)
Water depth: 8-9/16" (218 mm)

Drain hole: 3-5/8" (92 mm)

Template: Undermount, 1315846-7, required, included

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.

Use the supplied cut-out template to select either a hidden or exposed rim.

Minimum base cabinet width: 33"-36" (33" cabinet may require cabinet modifications). Consult an installer for confirmation before proceeding.