



McAllister®

23-1/2" undermount single-bowl kitchen sink, 40 pack F24738

Features

- Undermount rimless design
- Single bowl
- Wide undermount lip
- 23-3/8" (594 mm) x 17-11/16" (449 mm) x 5-15/16" (151 mm)
- Sink is available in single or multipacks
- 24738 = Single pack
- J24738 = 3 per pack
- T24738 = 20 per pack
- F24738 = 40 per pack
- Sink drain with strainer sold separately

Material

- Premium 18-gauge stainless steel

Recommended Products/Accessories

K-23729 Stainless steel cleaner

Optional Products/Accessories

7400 Stainless Steel Sink Drain and Strainer



ADA

Codes/Standards





ASME A112.19.3/CSA B45.4

ADA

ICC/ANSI A117.1

STERLING® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.



Mounting bracket assembly provides a secure installation.

Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Bowl area (Only): Length: 21" (533 mm)
Width: 15-1/4" (387 mm)
Bowl depth: 5-5/8" (143 mm)
Water depth: 5-5/8" (143 mm)

Drain hole: 3-3/4" (95 mm)

Template: 1315840-7, required, included

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.