



McAllister®

32" undermount double-bowl kitchen sink, 40 pack

F24765

Features

- No faucet holes; requires wall- or counter-mount faucet
- 5-15/16" depth
- 3-3/4" (94 mm) drain opening
- Stainless steel with luster finish

Material

- Premium 18-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- 7400 Stainless Steel Sink Drain and Strainer



ADA


Codes/Standards

ASME A112.19.3/CSA B45.4
ADA
ICC/ANSI A117.1

STERLING® Stainless Steel Sinks

Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration: Equal Bowls

Bowl area: Length: 14-1/8" (358 mm)
Width: 15-3/4" (400 mm)
Bowl depth: 5-5/8" (143 mm)
Water depth: 5-5/8" (143 mm)

Drain hole: 3-3/4" (95 mm)

Template: 1315846-7, required, included

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.