



## Southhaven®

33" top-mount single-bowl kitchen sink, 40 pack  
**F24912-4**

### Features

- Four faucet holes
- 8" (203 mm) depth
- 3-5/8" (92 mm) drain opening
- Stainless steel with luster bowl finish and a satin deck finish
- 40-pack

### Material

- Premium 20-gauge stainless steel

### Installation

- Top-mount

### Recommended Products/Accessories

K-23729 Stainless steel cleaner

### Optional Products/Accessories

7400 Stainless Steel Sink Drain and Strainer




### Codes/Standards

ASME A112.19.3/CSA B45.4

### STERLING® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Bowl area (Only): Length: 29-3/16" (742 mm)  
Width: 15-1/16" (383 mm)  
Bowl depth: 8" (203 mm)  
Water depth: 8" (203 mm)

Number of deck holes: 4

Faucet hole(s): 1-7/16" (37 mm)

Drain hole: 3-5/8" (92 mm)

### Notes

Install this product according to the installation instructions.