

**Features**

- Metal Framed Mirrored Cabinet
- All cabinets are non-handed/reversible
- Mirrored interior with 3 adjustable, cantilevered glass shelves
- Cantilever shelving adjustable in 1" increments
- Includes installation hardware for recess mounting
- Can be recessed or surface mounted (surface mounting kit required)
- Blum 155° slow close hinges

**Optional Features & Upgrades**

- PORTRAY Quick Caddy (QUICKCADDY)
- PORTRAY Electric Upgrade (P2ELECTRIC)
- Other widths/heights available: 24" wide, 40" high
- Glass Bins (GLASSBIN3.25, GLASSBIN5.25, GLASSBIN8.5)

**Construction**

- Rust free Satin anodized aluminum construction
- Blum hinges standard
- 3 mirror design - rear of cabinet and both sides of door

**Codes/Standards Applicable**

- Electric Option Models are ETL certified to:
  - UL 962
  - CSA Standard C22.2 No. 68


**Dimensions**

Width: 19-1/4" (489 mm)  
 Height: 30" (762 mm)  
 Depth: 4-3/4" (121 mm) When surface mounted  
 1-1/16" (26 mm) When recessed

**Installation Options**

**Recessed Mount** - Rough Opening - 18-1/2" W x 29-1/4" H x 4" D (470 mm W x 743 mm H x 102 mm D)

**Surface Mount (Single Cabinet)** - Reference Surface Mount Kit when ordering (P2SMKIT)



**Model Number Key**

Craft Cabinet Series	Width	Height	Depth	Frame Style	Frame Finish	Package Option
CC	20	30	D4	ND = Industrial Metal	34 = Iron Black w/ Brushed Pewter Accent 35 = Industrial Bronze w/ Aged Brass Accent	SC = Slow Close TU = Slow Close, Electric Upgrade

