

**Inline Sconce**  
**MLC40IKSSVCK Specification Sheet**

**FEATURES**

- Seamless, flush aesthetic
- Designed for easy installation as a standalone vertical sconce
- Provides programmable task lighting
- Tunable and dimmable when paired with a SWAY™ Controller
- Dimmable LED lighting to 5%
- Energy efficient LEDs with an estimated life of 53,000 hours:

Color Temperature (Kelvin)	2700K - 5600K
CRI	90+
R9 Value	60 - 80+
Source Lumens	1593 - 1889
Delivered Lumens	659 - 778

**MATERIALS & CONSTRUCTION**

- Rust free anodized aluminum and glass construction
- Anodized aluminum base structure
- Quality polished edge mirror finish
- Built-in diffuser delivers consistent, even light output
- Fully encased construction eliminates visibly exposed LEDs and electrical components
- Wired internally - Front access serviceability
- Requires Sway™ Controller to operate (sold separately)

**CODES & STANDARDS**

Certified for damp locations to:

- UL 8750
- CSA C22.2 No. 250.13
- Title 24 Certified

**DIMENSIONS**


- Width: 3-1/2" (89 mm)
- Height: 39-3/8" (1000 mm)
- Depth: 1-1/4" (32 mm)

**MORE INFORMATION**




Scan the QR code to see the rough opening and electrical details found in the Tunable Inline Sconce installation instructions.

Use the camera app on your mobile device to look at this QR code. This will allow you to quickly access web pages and other relevant documents.



Included Electrical Enclosure (Power Supply):



**MODEL NUMBER KEY**

	WIDTH	HEIGHT	DESIGN	QTY OF LIGHTS	BODY COLOR	COLOR TEMP	LED Engine
ML	C = 3-1/2"	40 = 39-3/8"	I = Inline	KS = Single Light	S = Silver	V = 2700K - 5600K	CK = Tunable

**OPTIONS**

- Other heights / LED engine / mounting options available

**ELECTRICAL SYSTEM**

- Operates on 120VAC 60Hz @ 0.6A Max per Power Supply
- Requires Sway™ Controller to operate (sold separately)
- Includes 6' (1.8 m) CAT5 Cable to connect Sway Controller

**INSTALLATION OPTIONS**

- Remote Power Supply Accessories (sold separately):
  - 15' (4.6 m) DC Cable Extension - SPS-EXTEND15
  - 30' (9.1 m) DC Cable Extension - SPS-EXTEND30
- **Electrical Enclosure Rough Opening:**  
**2.0" (51 mm) W x 15-1/2" (394 mm) H**

