

Inline Light

MLC30IKSSVC Specification Sheet

FEATURES

- Seamless, flush aesthetic
- Modular - combines with multiple cabinet lines
- Provides programmable task lighting
- Tunable and dimmable when paired with a SWAY™ Controller
- Dimmable LED lighting to 5%
- Energy efficient LEDs with an estimated life of 53,000 hours:

Color Temperature (Kelvin)	2700K - 5600K
CRI	90+
R9 Value	60 - 80+
Source Lumens	1260 - 1494
Delivered Lumens	570 - 740

MATERIALS & CONSTRUCTION

- Rust free anodized aluminum and glass construction
- Anodized aluminum base structure
- Quality polished edge mirror finish
- Built-in diffuser delivers consistent, even light output
- Fully encased construction eliminates visibly exposed LEDs and electrical components
- Wired internally - Front access serviceability
- Requires Sway™ Controller to operate (sold separately)

CODES & STANDARDS


Certified for damp locations to:

- UL 8750
- CSA C22.2 No. 250.13
- Title 24 Certified

DIMENSIONS

- Width: 3-1/2" (89 mm)
- Height: 30" (762 mm)
- Depth: 4-5/8" (118 mm) When surface mounted
15/16" (23 mm) When recessed

MORE INFORMATION




Scan the QR code to see the rough opening and electrical details found in the Tunable Inline Light installation instructions.


Use the camera app on your mobile device to look at this QR code. This will allow you to quickly access web pages and other relevant documents.

MODEL NUMBER KEY

	WIDTH	HEIGHT	DESIGN	QTY OF LIGHTS	BODY COLOR	COLOR TEMP	LED Engine
ML	C = 3-1/2"	30 = 30"	I = Inline	KS = Single Light	S = Silver	V = 2700K - 5600K	C = Tunable



Included Electrical Enclosure (Power Supply):



OPTIONS

- Other heights / LED engine / mounting options available

ELECTRICAL SYSTEM

- Operates on 120VAC 60Hz @ 0.6A Max per Power Supply
- Requires Sway™ Controller to operate (sold separately)
- Includes 6' (1.8 m) CAT5 Cable to connect Sway Controller

INSTALLATION OPTIONS

- Compatible Cabinet Mounting Kits (Single Cabinet):
 - Surface Mount Kit (P2SMKIT30D4P)
- Gangs between multiple cabinets via:
 - Surface Mount Ganging Kit (P2SM-GKIT30D4P)
 - Recessed Ganging Kit (P2RMGKIT)
- Compatible with M Reserve, Profiles, and PL Portray
- **Recessed Mount Rough Opening:**
Cabinet RO W + 3-1/2" W per light x 29-1/4" H
(Cabinet RO W + 89 mm W per light x 743 mm H)

