



1543353-T2

记录您的型号:

Record your model number: \_\_\_\_\_

**警告: 存在人身伤害风险。** 该产品内部有磁铁。产品应远离起搏器。

**警告: 存在烫伤风险。** 水温过高会导致严重灼伤。将阀芯水温设置在 120° F (49° C) 或以下。请参阅阀芯的温度调节说明。

**小心: 存在产品损坏和人身伤害风险。** 产品应远离加热器。

**提示:** 手持花洒的最高工作压力为0.5兆帕 (5巴)。如果压力超过0.5兆帕 (5巴), 请安装减压器。

**提示:** 淋浴器加施的水效标识表明本产品的水效等级等性能符合GB 28378-2019《淋浴器水效限定值及水效等级》的要求, 是产品符合性的一种标识。

请遵守当地管路安装及建筑条例。

1A. 安装软管之前, 先冲洗管道中的杂质 (本品不包含软管)。

2A. 如有需要, 安装花洒限流器。

4A. 定期打开水流, 擦拭花洒出水嘴, 去除杂质。

5A. 定期冲洗滤网垫圈, 去除杂质。

6A. 微气泡水。

6B. 亲氧水流技术。

7A. 按住按钮, 然后将把手伸缩到所需的长度, 以增加触达范围。松开按钮。

**需要帮助?** 请联系我们的客户服务中心。

• 中国大陆: + (86) 800-820-2628, + (86) 400-820-2628

• 中国香港、中国澳门、中国台湾: + (852) 3125-7728

有关质保信息, 请参阅科勒包装随附的合格证。


**WARNING: Risk of personal injury.** The product has a magnet inside. Keep the product away from a pacemaker.

**WARNING: Risk of scalding.** High water temperature can cause severe burns. Set the valve water temperature at or below 120°F (49°C). Refer to the temperature adjustment instructions for the valve.


**CAUTION: Risk of product damage and personal injury.** Keep the product away from a heater.

**NOTE:** The highest working pressure for a handshower is 0.5 MPa (5 bar). If the pressure exceeds 0.5 MPa (5 bar), a pressure reducer is needed.


1




2



3



4



**NOTE:** The water efficiency label applied to the shower indicates that the water efficiency grade and other performance of the product meet the requirements of GB 28378-2019 "Minimum Allowable Values of Water Efficiency and Water Efficiency Grades for Showers" which is a marking of product conformity. Follow all local plumbing and building codes.

**1A.** Flush the debris before installing the hose (not provided).

**2A.** If needed, install the flow restrictor.

**4A.** Periodically rub debris from the nozzles while water is running.

**5A.** Periodically rinse debris from the screen washer.

**6A.** MicroBubble spray.

**6B.** Katalyst™ air-induction.

**7A.** Press and hold the button, and slide the handle to the required length to increase the reach. Release the button.

**Need help?** Contact our Customer Care Center.

- Mainland China: +(86) 800-820-2628, +(86) 400-820-2628

- Hong Kong (China), Macau (China), Taiwan (China): +(852) 3125-7728

For warranty information, refer to the packed KOHLER compliance certificate.

