



# Triton® Bowe® | K-100T70-5ANL

0.5 gpm monoblock gooseneck bathroom sink faucet with laminar flow and wristblade handles, drain not included

## Features

- Quarter-turn washerless ceramic disc valves
- Vandal proof wristblade handles
- Swivel/rigid gooseneck spout
- 0.5 gpm (1.9 lpm) maximum flow rate at 60 psi (4.14 bar)
- Vandal-resistant laminar outlet



## Sustainability



## Available Colors/Finishes

*Color tiles intended for reference only.*

- CP Polished Chrome



1-800-4KOHLER (1-800-456-4537)  
Kohler Co. reserves the right to make revisions without notice to product specifications.  
For the most current specification sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada.  
4-15-2026 3:23 - US-CA

THE BOLD LOOK  
OF **KOHLER**

## Codes/Standards

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

ADA CSA B651 OBC

ASME A112.18.1/CSA B125.1  
NSF/ANSI/CAN 372  
NSF/ANSI/CAN 61  
DOE - Energy Policy Act 1992  
California Energy Commission (CEC)  
ADA  
ICC/ANSI A117.1  
CSA B651  
OBC

## Warranty

See website for detailed warranty information.

KOHLER® One-Year Limited Warranty

## Technical Information

All product dimensions are nominal.

### Handle

Handle Style/ Type: Lever

### Spout

Spout Reach: 5-3/16" (132 mm)

### Flow Rate

Faucet Flow Rate: 0.5 gpm (1.9 l/min)

## Valves

Included Valves: Ceramic disc, Thermostatic Mixer


## Material

- Brass
- Brass valve bodies

## Recommended Products/Accessories

K-23723 Faucet cleaner





## Installation

- Single-hole installation

## Installation Notes

*Install this product according to the installation instructions.*

ADA compliant for handles only.  
 ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

