

Features

- Katalyst® Spray Technology with air induction ball joint.
- Optimized sprayface for maximum performance.
- Single-function showerhead with 48 nozzle 5-1/2" (140 mm) diameter sprayface.
- Complements Forté® Suite.
- MasterClean® spray nozzles to prohibit mineral build-up for easy cleaning.
- 1/2" - 14 NPT connection.
- 2.0 gpm (7.6 l/min) maximum flow rate.

Material

- KOHLER finishes resist corrosion and tarnishing.

Installation

- Shower arm and flange sold separately.

Recommended Products/Accessories

K-7397 Shower Arm and Flange
K-23723 Faucet cleaner



Codes/Standards
EPA WaterSense®


KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	G	Brushed Chrome
	BRZ	Oil-Rubbed Bronze
	2BZ	Oil-Rubbed Bronze



Technical Information

All product dimensions are nominal.

Showerhead/Body Spray:

Rated maximum flow: 2 gal/min (7.6 l/min)

Pressure: 80 psi (5.5 bar)

Notes

For use with automatic compensating valves rated at 1.7 gal/min (6.4 l/min) or less.

Install this product according to the installation guide.