

Features

- Operates via battery, plug-in AC power, or Hybrid Energy System (each sold separately)
- Design-forward aesthetic for commercial bathroom spaces
- Below-counter valving reduces the faucet footprint and provides easier service
- 0.35 gpm (1.3 lpm) maximum flow rate with vandal-resistant outlet
- On-demand usage with 30-second max. continual run cycle to prevent vandalism and save water
- 4" (102 mm) spout reach
- Pair with select KOHLER® soap dispensers and single or two-hole escutcheons for an easy retrofit
- Includes spout and control box assemblies, and standard mounting hardware
- Less drain
- Concealed mechanical mixer sold separately
- Complies with the Safe Drinking Water Act (SDWA)

Material

- Premium material construction for durability and reliability

Installation

- Single-hole mounting

Required Products/Accessories

[K-13480-A](#) AC Single Supply

or

[K-13481-A](#) Multi-Outlet Power Supply

or

[K-36264](#) DC-powered battery pack for commercial touchless faucets

or

[K-28520](#) High-efficiency battery pack for commercial touchless sensor faucets

Recommended Products/Accessories

K-13481 Multi-Outlet Power Supply

K-13480 AC Single Supply

K-24154 Mechanical mixing valve

Optional Products/Accessories

K-38166 8" two-hole escutcheon plate for Insight™ and Kinesis® lavatory faucets and soap dispensers

K-38167 4" two-hole escutcheon plate for Insight™ and Kinesis® lavatory faucets and soap dispensers

K-38168 8" two-hole escutcheon plate for Insight™ and Kinesis® lavatory faucets and soap dispensers

K-38169 4" two-hole escutcheon plate for Insight™ and Kinesis® lavatory faucets and soap dispensers



ADA

CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

All applicable US Federal and State material regulations

DOE - Energy Policy Act 1992

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

CSA B651

OBC


KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|---|------|-----------------|
|  | CP | Polished Chrome |



Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

110/220 V

Technical Information

All product dimensions are nominal.

Power source: Hardwire - AC and Plug - AC, not included

Faucet:

Flow rate: 0.35 gal/min (1.3 l/min)

Drain included: No

Drain with overflow: Yes

Spout:

Spout reach: 4" (102 mm)

Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.