

Components®

Touchless lavatory faucet with Kinesis® sensor technology and temperature mixer, DC-powered, 0.5

Features

- Kinesis[®] technology with concealed sensor allows for a clean aesthetic and provides extraordinarily accurate and reliable actuation in varying installation environments
- Below-counter valving reduces the faucet footprint and provides easier service
- Design-forward aesthetic for commercial bathroom spaces
- 0.5 gpm (1.9 lpm) maximum flow rate with vandal-resistant outlet
- AA battery-powered; up to four-year battery life (approx. 105,000 cycles)
- On-demand usage with 30-second max. continual run cycle to prevent vandalism and save water
- 18" (457 mm) stainless steel braided flexible supply hose for easy installation
- 5-3/4" (146 mm) spout reach
- Box includes spout assembly, grid drain, control box assembly, concealed mechanical mixer, four AA batteries, supply hose, and standard mounting hardware

Material

Brass spout

Installation

Deck-mount

Optional Products/Accessories

K-99799 Thermostatic Tempering Valve

K-13479-A 8" escutcheon plate for Insight[™] and Kinesis® faucet

K-13479-B 8" escutcheon plate for Insight[™] and Kinesis® faucet

K-13478-A 4" escutcheon plate for $\mathsf{Insight}^{\mathsf{TM}}$ and $\mathsf{Kinesis} \ensuremath{\mathbb{B}}$ faucet

K-13478-B 4" escutcheon plate for $\mathsf{Insight}^{\mathsf{TM}}$ and $\mathsf{Kinesis}^{\mathbb{R}}$ faucet

Included Components

K-7129-A Bathroom sink grid drain with overflow





Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 61 NSF/ANSI/CAN 372 DOE - Energy Policy Act 1992 California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 OBC

KOHLER® One-Year Limited

Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description



CP Polished Chrome



gpm K-104MT87-SANA


KOHLER, Faucets

Components®

Touchless lavatory faucet with Kinesis® sensor technology and temperature mixer, DC-powered, 0.5

gpm





Technical Information

All product dimensions are nominal.

Power source:	Battery - DC, included
Faucet flow rate:	0.5 gal/min (1.9 l/min)
Drain included:	Yes
Drain with overflow:	Yes
Drain tailpiece included:	Yes
0	

Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

Spout:

Spout reach: 5-3/4" (146 mm)

Pressure/fixture Supply Requirements

Fixture pressure
max (static):125 psi (861.8 kPa)Fixture pressure min
(static):20 psi (137.9 kPa)

