

### Features

- Frosted-glass shades
- Sconce can be positioned up or down, depending on room setting
- Coordinates with other products in the Devonshire collection
- Includes installation hardware
- Suitable for damp locations, per UL 1598
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing



### Codes/Standards

UL 1598  
CSA C22.2 No. 250.0  
cETL Listed  
ETL Listed


### KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	BNL	Brushed Nickel
	CPL	Polished Chrome
	BLL	Matte Black
	2GL	Brushed Moderne Brass
	BML	Black, Brass Trim
	GZL	



## Required Electrical Service

1.5 A

## Technical Information

All product dimensions are nominal.

Material:	Metal
Number of Lights:	3
Number of Shades:	3
Shade Type:	Frosted Glass
Hanging Type:	Non-hanging

## Notes

Install this product according to the installation guide.