



Tripoint® | K-10669

Touchless DC 1.28 gpf retrofit toilet flushometer

Features

- Fixture-mount design
- Includes four 1.5 V AA batteries
- Retrofit models require a control stop and vacuum breaker



Codes/Standards

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

ADA CSA B651 OBC

ASSE 1037/ASME A112.1037/CSA B125.37

ADA

ICC/ANSI A117.1

CSA B651

OBC

Pressure/Fixture Supply Requirements

Minimum Flowing Pressure: 25 psi (172.4 kPa)

Material

- Brass

Technology


- Electronic infrared sensor with Tripoint® technology for accurate activation
- Slow-closing piston technology

Warranty

See website for detailed warranty information.

KOHLER® Faucet Lifetime Limited Warranty





Installation

- Intended for toilet installations with 1-1/2" (38 mm) spud coupling connection

Installation Notes

Install this product according to the installation instructions.

IMPORTANT! Maintain a 6" (152 mm) minimum critical level above the fixture.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

