

Features

- Fixture-mount design
- Includes a 9V lithium battery

Material

- Brass

Technology

- Electronic infrared sensor with WAVE technology for accurate activation
- Slow-closing piston technology

Installation

- Intended for toilet installations with 1-1/2" spud coupling connection

Optional Products/Accessories

GP1118986 Flushometer Extension Kit
K-10313 Flushometer 12" rough-in kit



ADA

CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1
CSA B64
CSA B125.3
ASSE 1037/ASME A112.1037/CSA B125.37
EPA WaterSense®
ADA
ICC/ANSI A117.1
CSA B651
OBC

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

with a
over the fixture

1" IPS Supply

5" (127 mm) Max
4-3/8" (111 mm) Min

16-1/2" (419 mm) Max

*12" (305 mm)

6" (152 mm) Min

Ø 3" (76 mm)

5" (127 mm) Max
2-1/4" (57 mm) Min

Ø 2-5/8" (67 mm)

Ø 1-1/2" (38 mm)

1" (25 mm)

Min flow rate: 25 gpm (94.6 lpm)

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.