

### Features

- Fixture-mount design
- Includes 1.5V AA batteries

### Material

- Brass

### Technology

- Electronic infrared sensor with WAVE technology for accurate activation
- Slow-closing piston technology

### Installation

- Intended for urinal installations with 3/4" (19 mm) spud coupling connection

### Optional Products/Accessories

GP1118986 Flushometer Extension Kit



ADA

CSA B651

OBC


### Codes/Standards

ASME A112.18.1/CSA B125.1  
ASSE 1037/ASME A112.1037/CSA B125.37  
EPA WaterSense®  
California Energy Commission (CEC)  
ADA  
ICC/ANSI A117.1  
CSA B651  
OBC

### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

\*10-3/4" (273 mm) minimum with a  
6" (152 mm) critical level above the fixture



### Technical Information

All product dimensions are nominal.

Power source: Battery - DC, included

### Pressure/fixture Supply Requirements

Fixture pressure 80 psi (551.6 kPa)

max (static):

Min flowing 25 psi (172.4 kPa)

pressure:

Min flow rate: 10 gpm (37.9 lpm)

### Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.