

Features

- Includes four 1.5 V AA batteries
- Fixture-mount design

Material

- Brass

Technology

- Slow-closing piston technology
- Electronic infrared sensor with Tripoint® technology for accurate activation

Installation

- Intended for toilet installations with 1-1/2" spud coupling connection

Recommended Products/Accessories

K-23723 Faucet cleaner

Optional Products/Accessories

GP1118986 Flushometer Extension Kit

K-10313 Flushometer 12" rough-in kit



ADA

CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1

CSA B64


CSA B125.3

ASSE 1037/ASME A112.1037/CSA B125.37

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

*11-3/8" (289 mm) minimum with a
6" (152 mm) critical level above the fixture



Technical Information

All product dimensions are nominal.

Power source: Battery - DC, included

Pressure/fixture Supply Requirements

Fixture pressure max (static): 80 psi (551.6 kPa)

Min flowing pressure: 25 psi (172.4 kPa)

Min flow rate: 25 gpm (94.6 lpm)

Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.