

### Features

- Fixture-mount design
- Includes 1.5V AA batteries

### Material

- Brass

### Technology

- Electronic infrared sensor with Tripoint® technology for accurate activation
- Slow-closing piston technology

### Installation

- Intended for urinal installations with 3/4" (19 mm) spud coupling connection

### Optional Products/Accessories

GP1118986 Flushometer Extension Kit



ADA

CSA B651

OBC


### Codes/Standards

ASME A112.18.1/CSA B125.1  
CSA B64  
CSA B125.3  
ASSE 1037/ASME A112.1037/CSA B125.37  
ADA  
ICC/ANSI A117.1  
CSA B651  
OBC

### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

\*11-3/8" (289 mm) minimum with a  
6" (152 mm) critical level above the fixture



## Technical Information

All product dimensions are nominal.

Power source: Battery - DC, included

## Pressure/fixture Supply Requirements

Fixture pressure max (static): 80 psi (551.6 kPa)

Min flowing pressure: 25 psi (172.4 kPa)

Min flow rate: 10 gpm (37.9 lpm)

## Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.