



Consonance®
69-1/4" x 69-1/4" drop-in whirlpool bath w/
BodyMassage™
K-1111-VLN

Features

- 6 hydromassage jets can be individually adjusted for water flow and direction
- Variable-speed pump for adjusting hydromassage intensity
- Two sets of 10 backjets target the lower back and shoulders to relieve tension and encourage deep breathing
- Chromatherapy lighting allows you to select a preferred color scheme to suit your mood
- Built-in heater
- Remote control
- Spacious design accommodates up to two bathers
- Two distinct bathing wells and a cool-off area allow you to create your own experience
- Two pillows provided for added comfort

Material

- Acrylic

Hydrotherapy

- 8 effervescence ports deliver gentle, caressing bubbles
- Whirlpool
- Backjets
- Chromatherapy

Installation

- Drop-in or undermount

Required Products/Accessories

K-9696 Whirlpool 6-Jet Trim Kit

or

K-T37391 Rotary-turn bath drain trim

K-T37392 Rotary-turn bath drain trim

or

K-37385 rough-in cable drain, PVC, 45" cable

K-78439 45" cable bath drain

or

K-37383 Rough-in cable bath drain, PVC, 30" cable with tubing

K-78438 30" cable bath drain

Recommended Products/Accessories

K-1601 Bath/whirlpool footstop, removable

K-23726 Drain treatment



Codes/Standards

ASME A112.19.7/CSA B45.10

CSA B45.5/IAPMO Z124

ASTM E162

ASTM E662

UL 1795

CSA C22.2 No. 218.2

cUL Listed

UL Listed


**KOHLER® Plastic Baths and
Shower Bases Lifetime Limited
Warranty KOHLER® Hydrotherapy
Components Five-Year Limited
Warranty**

See website for detailed warranty information.



Consonance®

69-1/4" x 69-1/4" drop-in whirlpool bath w/
BodyMassage™
K-1111-VLN



Required Electrical Service

Two dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump, Heater: 220-240 V, 20 A, 50/60 Hz

Pump, Heater: 220-240 V, 20 A, 50/60 Hz

Technical Information

All product dimensions are nominal.

Drain location: Reversible

Basin area, bottom: 45" x 43" (1143 mm x 1092 mm)

Basin area, top: 57" x 57" (1448 mm x 1448 mm)

Weight: 340 lbs (154.2 kg)

Minimum floor load: 54 lbs/ft² (263.7 kg/m²)

Water depth: 19-1/2" (495 mm)

Water capacity: 170 gal (643.5 L)

Cutout: Drop-in, 68" x 68" (1727 mm x 1727 mm)

Electrical component rating: Pump: 220-240 V, 11 A, 50/60 Hz
Heater: 220-240 V, 6.25 A, 50/60 Hz
Pump: 220-240 V, 11 A, 50/60 Hz

Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Kit is required for under-mount installations (sold separately).

If installing a rim-mount faucet, make sure there is no interference above or below the deck before drilling any holes.

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

3-30-2025 21:40 - US/CA

THE BOLD LOOK
OF **KOHLER®**