# **Underscore®**



66" x 36" drop-in bath with Bask® heated surface **K-1136-W1** 

### **Features**

- Bask® heated surface creates spa-like relaxation with soothing warmth on your back, shoulders, and neck
- Customize the heat with three adjustable settings
- Integral lumbar support
- Slotted overflow allows for deep soaking

#### Material

Acrylic

#### Installation

- Reversible drain
- Drop-in or undermount
- Requires 110 V electrical service

# **Required Products/Accessories**

K-7271 Brass Slotted Overflow Bath Drain

or

K-7272 PVC Slotted Overflow Bath Drain

#### **Recommended Products/Accessories**

K-591 Under-Mount Installation Kit
K-1177 Vinyl Tiling-in Bead
K-23726 Drain treatment
K-23732 Tub & shower cleaner
K-31797 Slotted overflow bath drain kit

K-31795 Slotted overflow above-the-floor bath drain kit



#### Codes/Standards

CSA B45.5/IAPMO Z124 ASTM E162 ASTM E662 UL 1795 CSA C22.2 No. 218.2 IAPMO Certification cUL Listed UL Listed

KOHLER® Plastic Baths and Receptors Lifetime Limited WarrantyKOHLER® Hydrotherapy Components Five-Year Limited Warranty

See website for detailed warranty information.

#### Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
	0	White
	96	Biscuit
	95	Ice™ Grey
	7	Black Black™







# 66" x 36" drop-in bath with Bask® heated surface **K-1136-W1**



## **Required Electrical Service**

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Heated Surface: 120 V, 15 A, 60 Hz

#### **Technical Information**

All product dimensions are nominal.

Drain location: Reversible

Basin area, bottom: 44-1/2" x 26-1/2" (1130 mm x 673 mm)

Basin area, top: 60-1/4" x 30-1/4" (1530 mm x 768 mm)

Weight: 86 lbs (39 kg)

Minimum floor load: 58 lbs/ft² (283.2 kg/m²)

Water depth: 17-3/4" (451 mm)

Water capacity: 102 gal (386.1 L)

Cutout: Drop-in, 65" x 35" (1651 mm x 889 mm)
Electrical component Heated Surface: 120 V, 0.5 A, 60 Hz, 65

rating: W

Minimum flat for 2-7/16" (61 mm)

door:

#### **Notes**

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Kit is required for under-mount installations (sold separately).



Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current Specification Sheet, go to <a href="https://www.kohler.com">www.kohler.com</a> USA or <a href="https://www.kohler.com">www.kohler.ca</a> Canada 8-26-2024 22:22 - US/CA

