

## Features

- Single-speed whirlpool offers performance and value, with six fully adjustable jets
- Hydromassage flow and direction can be controlled at each jet
- Generous length provides a spacious bathing area
- Hourglass shape adds style and elegance to your bathroom
- Integral lumbar support and armrests offer extra comfort while bathing
- Integral flange helps prevent water from seeping behind wall and simplifies alcove installation

## Material

- Acrylic

## Hydrotherapy

- Whirlpool

## Installation

- Right drain
- Alcove

## Recommended Products/Accessories

K-1491 Bath/Whirlpool Pillow  
K-1601 Bath/whirlpool footstop, removable  
K-7213 27" Cable Bath Drain  
K-7214 27" Cable Bath Drain  
K-7265 Brass toe tap bath drain  
K-23726 Drain treatment



## Codes/Standards

ASME A112.19.7/CSA B45.10  
CSA B45.5/IAPMO Z124  
UL 1795  
UL Listed


This product has been discontinued.

**KOHLER® Plastic Baths and Shower Bases Lifetime Limited Warranty**  
**KOHLER® Hydrotherapy Components Five-Year Limited Warranty**



See website for detailed warranty information.

**DISCONTINUED** This product has been discontinued.

No change in measurements if connected with drain illustrated. (K-11677)



Pump/Control Access  
(If Apron Is Not Used)  
20" (508 mm) W x 15" (381 mm) H



### Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump: 120 V, 15 A, 60 Hz

### Technical Information

All product dimensions are nominal.

|                              |                                                   |
|------------------------------|---------------------------------------------------|
| Drain location:              | Right                                             |
| Basin area, bottom:          | 55" x 21" (1397 mm x 533 mm)                      |
| Basin area, top:             | 65" x 26" (1651 mm x 660 mm)                      |
| Weight:                      | 66 lbs (29.9 kg)                                  |
| Minimum floor load:          | 38 lbs/ft <sup>2</sup> (185.5 kg/m <sup>2</sup> ) |
| Water depth:                 | 15" (381 mm)                                      |
| Water capacity:              | 72 gal (272.5 L)                                  |
| Electrical component rating: | Pump: 120 V, 7.5 A, 60 Hz                         |
| Pump speed:                  | Single                                            |
| Minimum flat for door:       | 2-5/8" (67 mm)                                    |

### Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Bath may require shimming if installing an apron.