

Features

- 122 airjets release thousands of bubbles that surround, support, and massage the body
- Variable-speed blower lets you adjust massage intensity to 18 levels
- Zones of Control™ feature allows you to target massage to back, midsection, or feet
- Chromatherapy lighting allows you to select a preferred color scheme to suit your mood
- Lighted keypad control
- Integral lumbar support
- Slotted overflow allows for deep soaking
- Automatic and manual purge cycles remove residual water from air channels after use

Material

- Acrylic

Hydrotherapy

- BubbleMassage™
- Chromatherapy

Installation

- Drop-in or undermount

Required Products/Accessories

K-7271 Brass Slotted Overflow Bath Drain

or

K-7272 PVC Slotted Overflow Bath Drain

Recommended Products/Accessories

K-1491 Bath/Whirlpool Pillow

K-1601 Bath/whirlpool footstop, removable

K-590 Undermount kit for select 60" Underscore bath models

K-1177 Vinyl Tiling-in Bead

K-23726 Drain treatment



Codes/Standards

ASME A112.19.7/CSA B45.10

CSA B45.5/IAPMO Z124

ASTM E162

ASTM E662

UL 1795

CSA C22.2 No. 218.2


cUL Listed

UL Listed




KOHLER® Plastic Baths and Shower Bases Lifetime Limited Warranty KOHLER® Hydrotherapy Components Five-Year Limited Warranty

See website for detailed warranty information.

No change in measurements if connected with drain illustrated. (K-7272)



Blower Motor/Control Access
34" (864 mm) W x 15" (381 mm) H Min



Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Blower: 240 V, 15 A, 50/60 Hz

Technical Information

All product dimensions are nominal.

Drain location: Reversible
 Basin area, bottom: 42" x 23-1/2" (1067 mm x 597 mm)
 Basin area, top: 55-1/8" x 27-1/8" (1400 mm x 689 mm)
 Weight: 100 lbs (45.4 kg)
 Minimum floor load: 55 lbs/ft² (268.5 kg/m²)
 Water depth: 17-1/8" (435 mm)
 Water capacity: 81 gal (306.6 L)
 Cutout: Drop-in, 59-1/2" x 31-1/2" (1511 mm x 800 mm)

Electrical component rating: Blower: 240 V, 5 A, 50/60 Hz

Blower speed: Variable

Minimum flat for: 2" (51 mm)

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

2-2-2026 21:43 - US/CA

Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Kit is required for under-mount installations (sold separately).

If relocating the blower motor, do not relocate or alter the PVC tee or coiled flexible tubing connected to the blower. Follow the blower relocation instructions exactly. Provide access for servicing the blower.