



## Underscore® Rectangle

5' Whirlpool Bath

K-1168-H2

### Features

- 8 hydromassage jets can be individually adjusted for water flow and direction.
- Variable-speed pump for adjusting massage intensity.
- Built-in heater.
- Lighted keypad.
- Sloping backrest provides comfort.
- Slotted overflow allows for deep soaking.

### Material

- Acrylic.

### Hydrotherapy

- Whirlpool.

### Installation

- Requires K-7271 or K-7272 Clearflo slotted overflow bath drain and K-9698 jet trim kit (sold separately).
- Drop-in or undermount.

### Required Products/Accessories

K-7271 Brass Slotted Overflow Bath Drain  
K-9698 Flexjet® Whirlpool Trim Kit

or

K-7272 PVC Slotted Overflow Bath Drain  
K-9698 Flexjet® Whirlpool Trim Kit

### Recommended Products/Accessories

K-1491 Bath/Whirlpool Pillow  
K-1601 Bath/Whirlpool Footstop  
K-1703 Whirlpool Remote Control  
K-590 5' under-mount installation kit  
K-9497 2-1/2" Keypad Trim  
K-24916 Wireless Music Kit  
K-1177 Vinyl Tiling-in Bead  
K-23726 Drain treatment  
K-23732 Tub & shower cleaner



### Codes/Standards

ASME A112.19.7/CSA B45.10  
CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662  
UL 1795  
CSA C22.2 No. 218.2

### KOHLER® Plastic Baths and Receptors

#### Lifetime Limited Warranty

#### KOHLER® Hydrotherapy Components

#### Five-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

| Color                                                                                | Code | Description   |
|--------------------------------------------------------------------------------------|------|---------------|
|  | G9   | Sandbar       |
|  | 33   | Mexican Sand™ |
|  | K4   | Cashmere      |




## Underscore® Rectangle

5' Whirlpool Bath

K-1168-H2

No change in measurements if connected with drain illustrated. (K-7272)



### Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump: 240 V, 20 A, 50/60 Hz

### Technical Information

All product dimensions are nominal.

|                              |                                                   |
|------------------------------|---------------------------------------------------|
| Installation:                | Drop-in, Under-mount                              |
| Drain location:              | End                                               |
| Basin area, bottom:          | 42" x 23-1/2" (1067 mm x 597 mm)                  |
| Basin area, top:             | 55-1/8" x 27-1/8" (1400 mm x 689 mm)              |
| Weight:                      | 125 lbs (56.7 kg)                                 |
| Minimum floor load:          | 62 lbs/ft <sup>2</sup> (302.7 kg/m <sup>2</sup> ) |
| Water depth:                 | 17-1/8" (435 mm)                                  |
| Water capacity:              | 81 gal (306.6 L)                                  |
| Cutout:                      | Drop-in, 59-1/2" x 31-1/2" (1511 mm x 800 mm)     |
| Electrical component rating: | Pump: 240 V, 11 A, 50/60 Hz, 1500 W               |
| Pump speed:                  | Variable                                          |
| Minimum flat for door:       | 2" (51 mm)                                        |

### Notes

Measure your actual product for rough-in details. Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Kit is required for under-mount installations (sold separately).

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com).

4-15-2020 06:28 - US/CA

THE BOLD LOOK  
OF **KOHLER**