



K-11808

15" W x 26" H aluminum single-door medicine cabinet with mirrored door and white interior

Features

- Two adjustable tempered-glass shelves offer additional bathroom storage
- Full-overlay mirrored door
- White powder-coated interior
- Two-way adjustable hinges with 108° opening capability for easy cabinet access
- Includes side mirror kit for surface-mount installation
- Optional decorative Shaker frame available, K-99575-15



DISCONTINUED



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-29-2026 23:45 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

None Applicable

Technical Information

All product dimensions are nominal.

Cutout

Width:	14-1/4" (362 mm)
Height:	25-1/4" (641 mm)
Depth:	3-11/16" (94 mm)

Material

- Anodized aluminum construction with a durable rustproof and chip-resistant finish
- Powder-coated aluminum

Recommended Products/Accessories


K-23723 Faucet cleaner

Warranty

See website for detailed warranty information.

KOHLER® One-Year Limited Warranty





Installation

- Can be installed with left- or right-hand swing
- Includes mounting hardware for surface or recessed installation

Installation Notes

Install this product according to the installation instructions.

To determine the height of the cabinet, ensure the door will clear all obstacles (such as a faucet). A minimum 3" (76 mm) distance is required.

Secure the screws (provided) to a stud to avoid possible property and product damage. If this is not possible, anchors (not provided) must be inserted before installing the screws.

To recess mount, the wall cavity must be framed and the cabinet secured to framing studs. Reroute electrical or water supply lines from the cavity. Consult a professional if drain or vent piping is encountered, or if the wall is load-bearing.

Cutout for recess-mount installations: 14-1/4" (362 mm) width x 25-1/4" (641 mm) height x 3-11/16" (94 mm) depth.

