

## Features

- Metal construction
- One-piece, self-contained ceramic disc valve allows for both volume and temperature control
- High-temperature limit setting for added safety
- Lever handle
- 6" (152 mm) escutcheon plate
- 5" (127 mm) spout reach
- Metal pop-up drain with tailpiece
- Flexible supplies
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar)

## Recommended Products/Accessories

K-23726 Drain treatment



ADA

CSA B651


OBC

## Codes/Standards

ASME A112.18.1/CSA B125.1  
NSF/ANSI/CAN 61  
NSF/ANSI/CAN 372  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
California Energy Commission (CEC)  
ADA  
ICC/ANSI A117.1  
CSA B651  
OBC

## KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

**Spout:**

Spout reach: 5" (127 mm)

## Notes

Install this product according to the installation guide.

ADA compliant for handles only.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.