# **Mariposa®**



60" x 36" alcove Heated BubbleMassage™ air bath with Bask® heated surface, right drain K-1239-GHRW

### **Features**

- Bask® heated surface creates spa-like relaxation with soothing warmth on your back, shoulders, and neck
- Three heat settings allow you to customize the surface temperature
- 120 airjets release thousands of heated bubbles that surround and support the body in a warm massage
- Variable-speed blower lets you adjust massage intensity to 18 levels
- Heated BubbleMassage™ includes 60-minute automatic shutoff timer
- Two separate electronic keypad controls for Heated BubbleMassage™ and Bask®
- Hourglass shape adds style and elegance to your bathroom
- Integral flange helps prevent water from seeping behind wall and simplifies alcove installation
- Textured bottom surface
- Automatic and manual purge cycles remove residual water from air channels after use
- Bask® heated surface creates spa-like relaxation with soothing warmth on your back, shoulders, and neck

## Material

Acrylic

## **Technology**

 Heated BubbleMassage™ technology warms and humidifies air before it enters the bath

## Installation

Right drain

## Required Products/Accessories

K-T37391 Rotary-turn bath drain trim K-T37392 Rotary-turn bath drain trim

or

K-37383 Rough-in cable bath drain, PVC, 30" cable with tubing

K-78438 30" cable bath drain

## **Recommended Products/Accessories**

K-1446 Remote Installation Kit

K-1491 Bath/Whirlpool Pillow

K-1601 Bath/whirlpool footstop, removable

K-23726 Drain treatment

K-23732 Tub & shower cleaner

K-7265 Brass toe tap bath drain

K-7259 Brass toe tap bath drain

K-31796 Above-the-floor bath drain kit

K-91708 Rath drain kit



## Codes/Standards

ASME A112.19.7/CSA B45.10 CSA B45.5/IAPMO Z124 ASTM E162 ASTM E662 UL 1795 IAPMO Certification cUL Listed UL Listed

KOHLER® Plastic Baths and Shower Bases Lifetime Limited WarrantyKOHLER® Hydrotherapy Components Five-Year Limited Warranty

See website for detailed warranty information.

## **Available Colors/Finishes**

Color tiles intended for reference only.

**Color Code Description** 

0 White








60" x 36" alcove Heated BubbleMassage™ air bath with Bask® heated surface, right drain

K-1239-GHRW



## **Required Electrical Service**

Two dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Blower, Heated 120 V, 15 A, 60 Hz

Surface:

Air bath: 120 V, 15 A, 60 Hz

## **Technical Information**

All product dimensions are nominal.

**Drain location:** Right

Basin area, bottom: 46" x 24" (1168 mm x 610 mm) Basin area, top: 54" x 27" (1372 mm x 686 mm)

Weight: 112 lbs (50.8 kg) Minimum floor load: 56 lbs/ft<sup>2</sup> (273.4 kg/m<sup>2</sup>) 13-11/16" (347 mm) Water depth: Water capacity: 63 gal (238.5 L)

Electrical component Blower: 120 V, 10 A, 60 Hz

Heated Surface: 120 V, 0.5 A, 60 Hz, 65 rating:

Air bath: 120 V, 5 A, 60 Hz

### **Notes**

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Remote blower installation kit K-1446 is available for relocating the blower. Provide access for servicing the blower.

Do not relocate or alter the PVC tee or coiled flexible tubing connected to the blower. Follow the blower relocation instructions exactly.



For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

9-30-2024 21:27 - US/CA

