



30" top-/wall-mount single-bowl farmhouse kitchen

sink

K-12700

#### **Features**

- Fits minimum 30" (762 mm) apron sink base cabinet
- Single bowl
- 8-5/8" depth
- Integral apron and backsplash
- Two faucet holes
- Requires K-1814-P and service part 63002 for wall-mount installation (sold separately)

## Material

Vitreous china

#### Installation

Wall-mount or top-mount apron-front

## **Recommended Products/Accessories**

K-1814-P Wall-Mount Sink Brackets 63002 Bracket, Tie Bar K-23726 Drain treatment

## **Optional Products/Accessories**

K-6002 Sink Rack

K-8803 Manual Sink Basket Strainer

K-8804 Sink drain body with tailpiece

K-8813 Stainless steel sink drain and strainer with tailpiece

K-8814 Stainless steel sink drain and strainer

K-8807 Sink drain and strainer with tailpiece

K-11352 Disposal Flange with Stopper

K-9000 P-Trap



### Codes/Standards

ASME A112.19.2/CSA B45.1 IAPMO Certification

# KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

#### Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

0 White








30" top-/wall-mount single-bowl farmhouse kitchen

sink

K-12700



# **Technical Information**

All product dimensions are nominal.

Basin configuration: Single Bowl Min. base cabinet 30" (762 mm)

width:

Bowl area: Bowl depth: 8-5/8" (219 mm)

Number of deck

holes:

Faucet hole(s): 1-3/8" (35 mm)
Drain hole: 3-5/8" (92 mm)

#### **Notes**

Install this product according to the installation instructions.

