



24" top-/wall-mount single-bowl farmhouse kitchen

sink

K-12701

Features

- Fits minimum 24" (610 mm) apron sink base cabinet
- Single bowl
- 8-5/8" depth
- Integral apron and backsplash
- Two faucet holes
- Requires K-1814-P and service part 63001 for wall-mount installation (sold separately)

Material

Vitreous china

Installation

Wall-mount or top-mount apron-front

Required Products/Accessories

K-1814-P Wall-Mount Sink Brackets 63001 Bracket Tie Bar

Recommended Products/Accessories

K-23726 Drain treatment

Optional Products/Accessories

K-8803 Manual Sink Basket Strainer

K-8804 Sink drain body with tailpiece

K-8813 Stainless steel sink drain and strainer with tailpiece

K-8814 Stainless steel sink drain and strainer

K-8807 Sink drain and strainer with tailpiece

K-11352 Disposal Flange with Stopper

K-9000 P-Trap



Codes/Standards

ASME A112.19.2/CSA B45.1 IAPMO Certification

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

0 White








24" top-/wall-mount single-bowl farmhouse kitchen

sink

K-12701



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl Min. base cabinet 24" (610 mm)

width:

Bowl area: Bowl depth: 8-5/8" (219 mm)

Number of deck 2

holes:

Faucet hole(s): 1-3/8" (35 mm)
Drain hole: 3-5/8" (92 mm)

Notes

Install this product according to the installation instructions.

