



Gilford™

Bracket-mount scrub-up/plaster sink
K-12781

Features

- Single center hole drilled back
- 30" x 22"

Material

- Vitreous china
- Premium material construction for durability and reliability

Recommended Products/Accessories

- K-1814-P Wall-Mount Sink Brackets
- K-8820 Sink Drain and Strainer
- K-23726 Drain treatment

Optional Products/Accessories

- K-9000 P-Trap
- K-9115 Sink Strainer



Codes/Standards

ASME A112.19.2/CSA B45.1
IAPMO Certification

**KOHLER® One-Year Limited
Warranty**


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Basin configuration:	Single Bowl
Basin area (Only):	Length: 28" (711 mm) Width: 18" (457 mm) Water depth: 8-5/8" (219 mm)
Number of deck holes:	1
Faucet hole(s):	1-3/8" (35 mm)
Drain hole:	2-1/4" (57 mm)

Notes

Install this product according to the installation instructions.