



Gilford™ | K-12784

24" x 22" bracket-mount scrub-up/plaster sink with single faucet hole

Features

- Single center hole drilled back
- 24" x 22 1/8"



Available Colors/Finishes

Color tiles intended for reference only.

- 0 White



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
4-15-2026 2:58 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ASME A112.19.2/CSA B45.1

Technical Information

Number of Deck Holes:	1
Faucet Hole(s) Size:	1-3/8" (35 mm)
Drain Hole Diameter:	2-1/4" (57 mm)
Basin Configuration:	Single Bowl
Basin Length:	22" (559 mm)
Basin Width:	18" (457 mm)
Basin Depth:	9-1/2" (242 mm)

Material

- Vitreous china
 - Premium material construction for durability and reliability
-

Recommended Products/Accessories

K-23726 Drain treatment

K-8820 Brass sink strainer for 2" outlets

Required Products/Accessories

- K-1814-P Wall brackets
 - 63002 Bracket, Tie Bar
-

Warranty

See website for detailed warranty information.

KOHLER® Vitreous China Bathroom Sink Lifetime Limited Warranty




1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

4-15-2026 2:58 - US-CA



Installation Notes

Install this product according to the installation instructions.

Product dimensions are nominal and may vary per ASME A112.19.2 tolerances.

