



Gilford™

Bracket-mount scrub-up/plaster sink
K-12784

Features

- Single center hole drilled back
- 24" x 22 1/8"

Material

- Vitreous china
- Premium material construction for durability and reliability

Required Products/Accessories

[K-1814-P](#) Wall-Mount Sink Brackets
63002 Bracket, Tie Bar

Recommended Products/Accessories

K-8820 Sink Drain and Strainer
K-23726 Drain treatment

Optional Products/Accessories

K-9115 Sink Strainer



Codes/Standards

ASME A112.19.2/CSA B45.1
IAPMO Certification


KOHLER® Vitreous China Bathroom Sink Lifetime Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Basin configuration:	Single Bowl
Bowl area (Only):	Length: 22" (559 mm)
	Width: 18" (457 mm)
	Water depth: 8-5/8" (219 mm)
Number of deck holes:	1
Faucet hole(s):	1-3/8" (35 mm)
Drain hole:	2-1/4" (57 mm)

Notes

Install this product according to the installation instructions.