

Sculpted

Touchless single-hole lavatory faucet with Insight™ sensor technology, DC-powered, 0.35 gpm K-13461-SATA

Features

- 0.35 gpm (1.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- Factory-set 30-second maximum continual run cycle
- Vandal-resistant aerator
- 24" (610 mm) flexible supply hose for easy installation
- 5" (127 mm) spout reach
- Includes two AAA batteries
- Stationary spout
- Without temperature mixer
- Less drain

Material

Brass

Installation

- Single-hole mounting
- Above-counter battery and valve for easy installation and maintenance



ADA CSA B651 OBC

Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 372 All applicable US Federal and State material regulations DOE - Energy Policy Act 1992 California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 OBC

KOHLER® Electronic Faucets, Valves, and Controls Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description


CP Polished Chrome





Sculpted

Touchless single-hole lavatory faucet with Insight™ sensor technology, DC-powered, 0.35 gpm K-13461-SATA



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 0.35 gal/min (1.3 l/min)

Drain included: No Drain with overflow: Yes

Spout:

Spout reach: 4-15/16" (125 mm)

Handshower:

Rated maximum 0 gal/min (0 l/min)

flow:

Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

