

Features

- Powers up to eight Kohler Insight™ AC touchless faucets
- Input for 120 VAC, 50/60- Hertz operation
- Energy Star Efficiency Level VI
- Regulated output of 5 VDC at 1.2 amps
- Short circuit and over voltage output protection
- Intended for use in North America outlets only. For global outlets, please use K-13481-NA

Technology

- Switching power supply technology

Installation

- Designed for portable or permanent hardwire installations
- Supplied with 60" (1524 mm) power cord for easy 120-volt installation
- Rugged ABS construction

Required Products/Accessories

[K-13487](#) 4' Cable Assembly

or

[K-13602](#) 6' Cable Assembly

or

[K-13604](#) 10' Cable Assembly




Codes/Standards

UL 1310
cUL Listed
UL Listed

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required.

120/240 V, 0.3 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Plastic

Notes

Install this product according to the installation instructions.