

### Features

- Fixture-mount design

### Material

- Brass

### Technology

- Nonhold open piston technology for accurate activation

### Installation

- Intended for urinal installations with 3/4" (19 mm) spud coupling connection

### Optional Products/Accessories

- GP1118986 Flushometer Extension Kit



ADA

CSA B651

OBC

### Codes/Standards

ASME A112.18.1/CSA B125.1

CSA B125.3

CSA B64

ASSE 1037/ASME A112.1037/CSA B125.37

EPA WaterSense®

ADA

ICC/ANSI A117.1


CSA B651

OBC

### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

\*10-3/4" (273 mm) minimum with a  
6" (152 mm) critical level above the fixture



### Technical Information

All product dimensions are nominal.

### Pressure/fixture Supply Requirements

Fixture pressure max (static):	80 psi (551.6 kPa)
Min flowing pressure:	25 psi (172.4 kPa)
Min flow rate:	10 gpm (37.9 lpm)

### Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.