Contemporary | K-13696-G

Square 10" single-function rainhead, 1.75 gpm

Features

- Single-function rainhead
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Optimized sprayface for maximum performance
- 1.75 gpm (6.6 lpm) maximum flow rate

Sustainability

Available Colors/Finishes

Color tiles intended for reference only.

	CP	Polished Chrome
	SN	Vibrant Polished Nickel
	AF	Vibrant French Gold
	BN	Vibrant Brushed Nickel
	BV	Vibrant Brushed Bronze
	BL	Matte Black
	2MB	Vibrant Brushed Moderne Brass
	TT	Vibrant Titanium

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-08-2026 23:55 - US-CA

Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)

Technical Information

All product dimensions are nominal.

Flow Rate

Shower/Rainhead Rated Maximum Flow:	1.75 gpm (6.6 l/min)

Material

- Solid-brass construction for durability and reliability

Recommended Products/Accessories

- K-23723 Faucet cleaner

Technology

- Katalyst® air-induction technology infuses water with air, creating bigger drops for a more powerful spray

Warranty

See website for detailed warranty information.

KOHLER® Faucet Lifetime Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-08-2026 23:55 - US-CA

THE BOLD LOOK OF KOHLER.



Installation

- 1/2" -14 NPT connection

Installation Notes

Install this product according to the installation instructions.

For use with automatic compensating valves rated at 1.4 gal/min (5.3 l/min) or less.

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-08-2026 23:55 - US-CA

THE BOLD LOOK OF KOHLER.