KOHLER_®

Veil® Hidden cord one-piece elongated toilet with skirted trapway, dual-flush

K-1381-HC

Features

- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Elongated bowl offers added room and comfort
- Dual flush offers a choice of 0.8 or 1.28 gpf (3.0 or 4.8 lpf)
- Left-hand Polished Chrome trip lever
- 2-1/8" (54 mm) glazed trapway
- Skirted trapway simplifies cleaning
- Hidden cord design conceals bidet seat cords (bidet seat sold separately)
- Coordinates with other products in the Veil collection
- Includes bidet water inlet hose

Installation

Standard 12" (305 mm) rough-in

Recommended Products/Accessories

K-28821 PureWash® E930 Elongated bidet toilet seat with remote control

K-8298-CR PureWash® E820 Elongated bidet toilet seat with remote control

K-27142-CR PureWash® E700 Elongated bidet toilet seat with remote control

K-26132-CSP PureWash® E545 Elongated bidet toilet seat 1023457 Wax Ring/Hardware Kit

1265114 Connector Hose





Codes/Standards

ASME A112.19.2/CSA B45.1 ASME A112.19.14 DOE - Energy Policy Act 1992 EPA WaterSense® California Energy Commission (CEC) IAPMO Certification

KOHLER[®] Toilets and Seats Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description




0 White







Veil® Hidden cord one-piece elongated toilet with skirted trapway, dual-flush K-1381-HC



Technical Information

All product dimensions are nominal.		
Toilet type:	Floor-mount	
Waste Outlet:	Floor	
Bowl shape:	Compact elongated	
Flush type:	Class Five	
Trap passageway:	2" (51 mm)	
Water surface size:	9" x 7-1/2" (229 mm x 191 mm)	
Rim to water	5-3/8" (137 mm)	
surface:		
Rough-in:	12" (305 mm)	
Template:	Footprint, 1262234-7, not required, included	

Fixture Supply Requirements

Min static pressure:	20 psi (137.9 kPa)
Max static pressure:	80 psi (551.6 kPa)
Min flowing	15 psi (103.4 kPa)
pressure:	
Min flow rate:	1 gpm (3.8 lpm)

Notes

Install this product according to the installation instructions.



1-800-4KOHLER (1-800-456-4537) Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current Specification Sheet, go to <u>www.kohler.com</u> USA or <u>www.kohler.ca</u> Canada 7-3-2024 20:07 - US