

Features

- Sleek and contemporary design
- Two-function pull-out sprayhead allows you to switch from aerated stream to Sweep® spray
- ProMotion® technology's light, quiet braided hose and swiveling ball joint make the pull-out sprayhead easier and more comfortable to use
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 229 mm (9 inch) spout reach
- Single Lever handle allows for on/off activation, volume, and temperature control
- 7.5 lpm (2.0 gpm) maximum flow rate at 3.0 bar (43.5 psi)
- Flexible G 1/2 supply hoses for easy installation

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- For single-hole installation
- Deck-mount



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	VS	Vibrant® Stainless



Technical Information

All product dimensions are nominal.

Notes

Install this product according to the installation instructions.