# Memoirs® | K-1418-GH

72" x 42" drop-in Heated BubbleMassage™ air bath

## Features

- 122 airjets release thousands of heated bubbles that surround, support, and massage the body
- Variable-speed blower lets you adjust massage intensity to 18 levels
- Built-in heater
- Automatic and manual purge cycles remove residual water from air channels after use
- 60-minute automatic shutoff timer
- Spacious design accommodates up to two bathers
- Integral lumbar support
- Keypad control
- Textured bottom surface
- Coordinates with other products in the Memoirs collection

## Available Colors/Finishes

***Color tiles intended for reference only.***

| | |
|---|---|
| 0 | White |
| 96 | Biscuit |



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 01:58 - US-CA

## Codes/Standards

ASME A112.19.7/CSA B45.10
CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
UL 1795
CSA C22.2 No. 218.2
cUL Listed
UL Listed

## Technical Information

***All product dimensions are nominal.***

| | |
|---|---|
| Drain Location: | Center |
| Drain Hole Diameter: | 2-1/4" (57 mm) |
| Minimum Flat for Door: | 3-13/16" (97 mm) |
| Basin Area, Bottom: | 48" x 27" (1219 mm x 686 mm) |
| Basin Area, Top: | 60" x 30" (1524 mm x 762 mm) |
| Water Depth: | 16" (406 mm) |
| Water Capacity: | 94 gal (355.8 L) |
| Minimum Floor Load: | 54 lbs/ft$^2$ |
| Weight: | 156 lbs (70.8 kg) |
| Cutout: | Drop-in, 70-1/2" x 40-1/2" (1791 mm x 1029 mm) |

## Material

- Acrylic

## Recommended Products/Accessories

- K-1491 Bath/whirlpool pillow, removable
- K-1601 Bath/whirlpool footstop, removable

## Required Products/Accessories

- K-11677 Adjustable drain, 20-gauge brass, for 18-1/2" to 20-1/2" baths

or

- K-T37392 Rotary-turn bath drain trim
- K-T37391 Rotary-turn bath drain trim

or

- K-78439 45" cable bath drain
- K-37385 Rough-in cable drain, PVC, 45" cable, less horizontal tube

## Technology

- Heated BubbleMassage™ technology warms and humidifies air before it enters the bath

## Required Electrical Service

Two dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

| | |
|---|---|
| Blower: | 120 V, 15 A, 60 Hz |
| Heater: | 120 V, 15 A, 60 Hz |

## Electrical Component Ratings

| | |
|---|---|
| Power Cord Length: | 35" (889 mm) |
| Blower: | 120 V, 10 A |
| Heater: | 120 V, 5 A, 60 Hz |

## Warranty

***See website for detailed warranty information.***

KOHLER® Plastic Baths and Shower Bases Lifetime Limited Warranty
KOHLER® Hydrotherapy Components Five-Year Limited Warranty



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 01:58 - US-CA

THE BOLD LOOK OF KOHLER.




## Installation

- Drop-in
- Rear center drain

## Installation Notes

***Install this product according to the installation instructions.***

Measure your actual product for rough-in details.
The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-12-2026 01:58 - US-CA

THE BOLD LOOK OF KOHLER